

1x2, 2x2 Fused PM Fiber Coupler 1330, 1350, 1370, 1390nm

Features

Low Excess Loss High Power Handling Both Slow and Fast Axes Working Telcordia GR-1221 Compliant

Applications



Specifications

								Reden
Unit	Values							
nm	1330, 1350, 1370, 1390							
nm	±20							
dB	0.4							
dB	0.3							
%	1/99	2/98	5/95	10/90	20/80	30/70	40/60	50/50
dB	21.5/0.4	18.2/0.5	14.2/0.6	11.0/0.85	8.0/1.35	6.0/1.95	4.8/2.6	3.4
dB	≥18							
-	PM1300, PM1550							
dB	≥50							
dB	≥50							
mW	4000							
°C	-40 ~ +85							
°C	-40 ~ +85							
	nm nm dB dB % dB dB dB - dB dB dB mW	nm nm dB dB dB % 1/99 dB % 1/99 dB % 1/99 dB 21.5/0.4 dB - dB dB mW °C	nm nm dB dB dB % 1/99 2/98 dB % 1/99 2/98 dB 21.5/0.4 18.2/0.5 dB - dB dB dB mW ℃	nm 1 nm - dB - dB 2/98 5/95 dB dB 21.5/0.4 dB - C -	nm 1330, 1350, nm ±2 dB 0 dB 0 dB 0 dB 0 dB 0 % 1/99 2/98 5/95 10/90 dB 21.5/0.4 18.2/0.5 dB - ≥ - PM1300, dB = dB = GB = mW 40 °C -40 ~	nm 1330, 1350, 1370, 139 nm ± 20 dB 0.4 dB 0.4 dB 0.3 % 1/99 2/98 5/95 10/90 20/80 dB 21.5/0.4 18.2/0.5 14.2/0.6 11.0/0.85 8.0/1.35 dB ≥ 18 ≥ 18 - ≥ 50 ≥ 50 dB ≥ 50 $= 4000$ °C $-40 \sim +85$	nm 1330, 1350, 1370, 1390 nm ± 20 dB 0.4 dB 0.4 dB 0.3 % 1/99 2/98 5/95 10/90 20/80 30/70 dB 21.5/0.4 18.2/0.5 14.2/0.6 11.0/0.85 8.0/1.35 6.0/1.95 dB ≥ 18 ≥ 18 ≥ 18 ≥ 50 dB ≥ 50 dB ≥ 50 $= 4000$ $= 4000 - +85$ $= 400 - +85$ $= 400 - +85$	1330, 1350, 1370, 1390 nm 1330, 1350, 1370, 1390 mm ± 20 dB 0.4 dB 0.4 dB 0.3 % 1/99 2/98 5/95 10/90 20/80 30/70 40/60 dB 21.5/0.4 18.2/0.5 14.2/0.6 11.0/0.85 8.0/1.35 6.0/1.95 4.8/2.6 dB ≥ 18 ~ 11300 , PM1550 dB ≥ 50 MW 4000 $^{\circ}$ -40 ~ +85

^[1] EL=10 * log₁₀ (P_{in}÷(P_{out1}+P_{out2})), P=power in mW,

^[2] Test at room temperature without connectors. With connectors, IL+0.3dB, RL-5dB. For short wavelength, IL+1.5dB.

^[3] With connectors, ER-2dB,RL-5dB.

^[4] DIR=10 * log₁₀ (P_{out2}÷P_{out1}), or DIR=10 * log10 (P_{in2}÷P_{in1}), P=power in mW, test light input from Port1,

When test DIR at output port, coil all input fibers 3-5 turns around a 10-30mm diameter loop, This prevents back reflections into output port2, which would significantly lower DIR.

^[5] Higher power up to 20W available on request.

Coupling/Split Ratio Tolerance [1]


1/99%	±0.3%
2/98%	±0.5%
5/95%	±0.7%
10/90%	±1.0%
20/80%	±2.0%
30/70%	±2.0%
40/60%	±2.5%
50/50%	±3.0%

^[1] Test/calculate without connector loss.

Package Information

Port Configuration	1x2 or 2x2					
Fiber Length	1m, others on request					
Pigtail Type	250µm Bare Fiber	900µm Loose Tube	2mm/3mm Loose Cable			
Dimensions(mm)	φ3x40, φ3x54	φ3x54	90x16x9			
Approx Weight (g)	30	45	60			







Ordering Information

1	Туре	PS=PM Fiber Standard Coupler;
2	Grade	P=Grade P;
3	Port Type	1x2; 2x2;
4	Wavelength	1330; 1350; 1370; 1390;
5	Coupling Ratio	1/99; 2/98; 5/95; ; 50/50;
6	Pigtail Type	250=250µm Fiber; 900=900µm Loose Tube; 2000=2mm Loose Cable; 3000=3mm Loose Cable;
$\overline{\mathcal{O}}$	Fiber Type	P13=PM1300; P15=PM1550;
8	Length	1=1m; X=Other;
9	Connector	NE=None; FA=FC/APC; FC=FC/UPC; SA=SC/APC; SC=SC/UPC; LC=LC/UPC; XX=Others;
(10)	Package	3x54; 90x16x9;

Application Notes

Fiber Core Alignment

Note that the minimum attenuation for these devices depends on excellent core-to-core alignment when the connectors are mated. This is crucial for shorter wavelengths with smaller fiber core diameters that can increase the loss of many decibels above the specification if they are not perfectly aligned. Different vendors' connectors may not mate well with each other, especially for angled polished (APC).

Coupling / split ratio will be very strange comparing to OPNETI's test data if additional connector mating loss is added.

Fiber Bending Loss

A shorter fiber and straightening the fiber or with larger bend radius will be very helpful to get lower Excess Loss, especially for visible wavelength testing.

Fiber Cleanliness

Fibers with smaller core diameters (<5µm) must be kept extremely clean, contamination at fiber-fiber interfaces, combined with the high optical power density, can lead to significant optical damage. This type of damage usually requires re-polishing or replacement of the connector.

Maximum Optical Input Power

Due to their small fiber core diameters for short wavelength and high photon energies, the damage thresholds for device is substantially reduced than the common 1550nm fiber. To avoid damage to the exposed fiber end faces and internal components, the optical input power should never exceed above table specified, if higher power handling is needed, please contact OPNETI technicians.

Standard connector power handling max 1W(CW), Optical connectors can be removed and the device can be spliced into optical path at higher optical powers.

Optical Path

All of our fused fiber couplers are bidirectional, means that all ports can be used as an input.

Coupler split ratio configuration refer to:

https://opneti.com/uploads/couplerconfig.mp4